

# squeeze tube chart



LM-100

## Laundry Applications

Part Number	Pump Model	Flow Rate	Tube Material	Tuber Inner Dimensions (in)	Tuber Outer Dimensions (in)	Tube Length (in)	Inlet Fitting	Outlet Fitting	Quantity
HYD41-03109-642*	LM-100	18 oz/min	EPDM	1/4	1/2	12	None	None	1
HYD13-06720-10*	LM-100	18 oz/min	EPDM	1/4	1/2	12	None	None	10
HYD13-06720-100*	LM-100	18 oz/min	EPDM	1/4	1/2	12	None	None	100
HYD41-03109-643	LM-100	18 oz/min	EPDM	1/4	1/2	18	None	None	1
HYD10016007	LM-100	18 oz/min	Norprene	1/4	1/2	11	None	None	1
HYD41-03109-242	LM-100	18 oz/min	Santoprene	1/4	1/2	12	None	None	1
HYD13-07982-10	LM-100	18 oz/min	Santoprene	1/4	1/2	12	None	None	10
HYD13-04273-23110	LM-100	18 oz/min	Santoprene	1/4	7/16	10	None	None	10
HYD03-03109-142	LM-100	18 oz/min	Silicone	1/4	1/2	12	None	None	1
HYD13-07786-10	LM-100	18 oz/min	Silicone	1/4	1/2	12	None	None	10
HYD13-07786-100	LM-100	18 oz/min	Silicone	1/4	1/2	12	None	None	100
HYD03-03109-143	LM-100	18 oz/min	Silicone	1/4	1/2	18	None	None	1
HYD03-03109-131	LM-100	18 oz/min	Silicone	1/4	7/16	10	None	None	1
HYD13-07971-10	LM-100	18 oz/min	Silicone	1/4	7/16	10	None	None	10
HYD03-03109-442	LM-100	18 oz/min	Viton	1/4	7/16	12	None	None	1
HYD13-07977-10	LM-100	18 oz/min	Viton	1/4	7/16	12	None	None	10
HYD03-03109-431	LM-100	18 oz/min	Viton	1/4	7/16	10	None	None	1

\*Standard squeeze tube